

# RōCoil mV™

## MilliVolt Output Flex CTs

The DENT RōCoil mV™ Flexible Current Transformers have been designed for accurate measurement of AC current with a safe, millivolt output.



### KEY SPECIFICATIONS

4 Lengths	40 cm (16"), 60 cm (24"), 90 cm (36"), 180 cm (72")
4 Window Sizes	13 cm (5"), 19 cm (7"), 26 cm (10"), 52 cm (20")
4 Current Ranges*	16", 1000A, 10—1300A AC 24", 2000A, 30—2600A AC 36", 3000A, 30—3900A AC 72", 6000A, 60—6000A AC
Output Signal	333 mV AC at rated current Max output 1,665 mVAC
Accuracy	< 1% typical at 2% to 500% of rated current

\*Depending on meter compatibility. See ELITEpro™ and PowerScout™ specifications for details.

### ELECTRICAL

All accuracies specified at 20°C (±2°C) with RōCoil mV™ centered on conductor.

Output Signal	(16") 333 mV @ 1000A (24") 333 mV @ 2000A (36") 333 mV @ 3000A (72") 333 mV @ 6000A	1665 mV @ 5000A 999 mV @ 6000A 666 mV @ 6000A
Max Output		1.66VAC
Power Requirement		5-24 VDC, 30 mA Maximum
Wire Color		Red = Power (+) Black = Power (-) White = Signal (+) Green = Signal (-)
Phasing		Arrow Points Towards Load
Phase Shift		< 1° at rated current
Frequency Range		45-600 Hz
Linearity		± 0.2%
Conductor Position Sensitivity		± 2% maximum
Influence of External Field		± 1.5% maximum
Temperature Sensitivity		0.07% per °C

### MECHANICAL

Coil Material	Blue thermoplastic rubber, flame retardant UL 94 V-0 rated
Coupling Materials	Polypropylene UL 94 V-0 rated
Case Material	ABS UL 94 V-0 rated
Shielding	85% transducer, 100% output lead
Working Temp	-20 °C to +60 °C (-4° to +140 °F)

### SAFETY

Working Voltage	600 Vrms maximum
Dielectric Strength	7400 VAC around coil 600 VAC rated leads
Certifications	Conforms to UL STD 61010-1 Certified to CAN/CSA STD C22.2 No. 61010




### RōCoil mV™ PART NUMBERS\*

16" RōCoil mV™	CT-RMV-16-1000	333 mV @ 1000A
24" RōCoil mV™	CT-RMV-24-2000	333 mV @ 2000A
36" RōCoil mV™	CT-RMV-36-3000	333 mV @ 3000A
72" RōCoil mV™	CT-RMV-72-6000	333 mV @ 6000A


\*Other Sizes, currents, and outputs are available. Please contact the factory for details.

### AVAILABLE OPTIONS

*PX-ADPT	Power Cable from Line-Powered ELITEpro™ for powering up to 4 CTs
*PX-ADPT-ESP	Adapter and Power Cable for powering up to 4 RōCoil mV CTs from the ELITEpro SP™.
*PX-XFMR-ESP	Wall Transformer plus Power Cable capable of powering up to



DIMENSIONS		RMV-16	RMV-24	RMV-36	RMV-72
<b>A</b>	Window Size	13 cm (5")	19 cm (7")	26 cm (10")	56 cm (22")
<b>B</b>	Transformer Coil O.D.	15 cm (6")	21 cm (8")	29 cm (11")	58 cm (23")
<b>C</b>	Transformer Length	40 cm (16")	60 cm (24")	90 cm (36")	180 cm (72")
<b>D</b>	Locking Connector O.D.	3.6 cm (1.4")			
<b>E</b>	Transformer Coil Diameter	1.5 cm (0.6")			
<b>F</b>	Wire Lead Total Length	2 m (80")			
<b>G</b>	Length of mV Module	9.5 cm (3.8")			
<b>H</b>	Width of mV Module	3.2 cm (1.3")			



### CONTACT US

DENT Instruments, Inc.  
Energy & Power Measurement Solutions

925 SW EMKAY DRIVE  
BEND, OREGON 97702 USA  
541.388.4774 | 800.388.0770  
WWW.DENTINSTRUMENTS.COM